



## 2024-2025 Field Compliance Check

All events are expected to meet the minimum compliance requirements:

- For single day events Checks must be completed once, prior to the start of qualification matches •
- Additionally, for multi day events Checks must be completed prior to the start of matches EACH day •

#	Color		$\nabla \nabla \nabla$	Spec & (Tolerance)	Inspection Item Description		
Sam	nple Prese	t Lir	ies / Spike Mar	ks (See Field Setup Gu	iide: "Sample Preset Lines")		
1.1	RED:			3.5" (+/- 0.25")	Tape Length is Correct and		
1.1				0.0" (+/- 0.25")	Tape Edge starts adjacent to Tile Seam		
1.2	RED: BLUE: WHITE:			0.0" (+/- 0.25")	For the (4) Lines closest to Submersible (ref image 1.2): Confirm the Tape Side is Adjacent to Tile Seam		
1.3	RED: BLUE: WHITE:			10.0" (+/- 0.25")	Tape to Tape Spacing – As Shown in Ref Images & Setup Guide (NOT the gap between tape lines)		
Bas	ket Height	s (S	ee Figure 9-10	in manual section 9.6)			
2.1	RED:		BLUE: 🗌	25.75" (+/- 0.25")	Height of LOW BASKET Front Lip to Tile Surface		
2.2	RED:		BLUE: 🗌	43.0" (+/- 0.25")	Height of HIGH BASKET Front Lip to Tile Surface		
Sub	mersible S	Struc	cture & Ascent	Zone (See manual sec	tion 9.5 & Field Setup Guide)		
3.1	RED:		BLUE:	10.0" (+/- 0.25")	ASCENT ZONE Tape: Tape Apex from the Tile Seam		
3.2	RED:		BLUE:	13.0" (+/- 0.5")	Height of top of LOW CHAMBER above Tile Surface		
3.3	RED:		BLUE:	26.0" (+/- 0.5")	Height of top of HIGH CHAMBER above Tile Surface		
3.4	RED:		BLUE:	20.0" (+/- 0.5")	Height of top of LOW RUNG above Tile Surface		
3.5	RED:		BLUE: 🔲	36.0" (+/- 0.5")	Height of top of HIGH RUNG above Tile Surface		
Apri	ITags (Se	e ma	anual section 9	.8 & "AprilTag Images"	in the Playing Field Materials)		
4.1	11 14	1 []	2 13 5 16	4.0" (+/- 0.25")	AprilTag Height: Alignment Line above Tile Surface [Check each tag (2x): Right Edge, Left Edge]		
4.2	11		2 13 1 5 16	0.0" (+/- 0.375")	AprilTag Horizontal Alignment: Centered on Tile Junction (mid of "saw tooth" pattern)		
Clip	s (See ma	nual	section 9.7.2)				
5.1	Check Clips as Shown (40x) per Field			0.75" (+/- 0.125")			
- Note	<ul> <li>Clips can be manually re-adjusted to spec by bending the plastic.</li> <li>Note, this new dimension was specifically identified for compliance checks.</li> <li>Revision v1 - Feb 19, 2025</li> </ul>						





firstinspires.org/robotics/ftc

## **REFERENCE IMAGES:** (Refer to the Competition Manual & "Field Assembly and Setup Guide" for more details)











firstinspires.org/robotics/ftc

**REFERENCE IMAGES cont:** (Refer to the Competition Manual & "Field Assembly and Setup Guide" for more details)



Revision History					
Revision	Date	Description			
1	2/19/2025	Initial Release			